

U.S.A. 630.860.7447 x2258 United Kingdom 08000 964396 Germany 040 4231600 Belgium +31 20-697-7171 Netherlands 020-697-7171

Operating Instructions

CALUMET ON-SITE™ PORTABLE BACKGROUND SYSTEM

The Calumet On-SiteTM Portable Muslin Background System assembles in minutes. It contains a unique patented X-frame which consists of four arrow rods, four straight rods with silver connector units, a round connector hub with thumbscrew, one spare thumbscrew, a convenient adjustable stand and a $8 \times 8 \times 36$ " carrying case. This system is recommended for indoor use only. It weighs 12.8 lbs. $\{5.8kg\}$. **MP0500**

1.)




Start with one arrow rod and one straight rod. Connect the rods by inserting the square end of the straight rod into the silver connector on the arrow rod. While connecting the rods, ensure that both are placed with the rounded side facing up. Repeat this step with remaining pairs of rods.

2.)



Place the four assembled rods on the floor with the label or rounded side facing down. Next, position the round connector hub (label down) and insert each rod into the four slots found on the unit, forming an "X." Note: The arrow on the round connector hub should be pointing downward, so that when you lift the unit, it is pointing toward the floor.

3.)



Position your muslin fabric face up over the X-frame and slide each corner of the fabric onto the arrow rods. The fabric will stretch and cover the span of the X-frame

4.)



Lift the assembled X-frame off the floor and place it onto the stud of the adjustable stand. Secure to stand by tightening thumbscrew on the round connector hub.

5.)



Adjust stand to desired height. The bottom corners of the fabric panel should rest on the floor to provide additional stability. The use of Calumet sandbags are recommended for ultimate stability.

6.)



The Calumet On-Site $^{\text{\tiny{TM}}}$ Portable Muslin Background System is now completely assembled.

7.)



The 8 x 8' muslin fabrics are available in a variety of different colors and are sold separately, or can be purchased in complete On-SiteTM System Kits. Visit calumetphoto.com for details.